

YOSEMITE | sliding shower set

Finish: polished chrome (CR)



Technologies



The EASY CLEAN nozzles allow the user to easily remove any limescale build up by simply wiping their silicone surface.



The EASY MOUNT system enables quick and easy product assembly, with no tools required.



The sliding bar is equipped with the FLEXI FIX system which allows the user to choose a desired height for the mounted elements. Any existing mounting holes, if these exist, may be easily and precisely matched.

Flow characteristics

- hot water supply: max. 90 °C
- working pressure 1-5 bar

Specification

- hand shower, 5-function, streams: massage, mist, aerated rain, aerated massage, aerated mist
- stainless steel sliding bar, length: 90.5 cm, distance between mounting brackets: 24-85 cm
- PVC-coated flexible shower hose (SILVER-X175SL), length: 175 cm

Product care

What is the best way to care for a hand shower ?

Remember to regularly wipe the silicone nozzles with your hand to remove any limescale deposits that might be forming on their surface. A toothpick or toothbrush can also be used to clean the spaces in between if there is a considerable build-up of limescale.

For more stubborn dirt, it is recommended to immerse the hand shower in a 10% citric acid solution with water for about 10 minutes to soften the limescale and then wipe across the nozzles with a soft brush. It is not recommended to use rough or abrasive materials and corrosive or bleaching substances to prevent damaging the surface of the product. From time to time, it is recommended to unscrew the hand shower and flush it from the inside to remove any dirt preventing the flow of water.

